

**Rittal – The System.**

Faster – better – everywhere.



**SV 9343.110**

**NH Fuse-Switch Disconnectors**

State: 4/28/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9343.110 - NH Fuse-Switch Disconnectors

## Features

Model No.	SV 9343.110
Version	For 60 mm busbar systems
Material	Polyamide Fire behavior corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated
Color	Chassis: RAL 7035 Cover: RAL 7035/7001
Clamping area for laminated copper bars:	Clamping area width: 32 mm Clamping area height: 10 mm Clamping area width: 1.26 " Clamping area height: 0.39 "
For bar systems with center-to-center spacing	60 mm
Cable outlet	Top/bottom
Type of connection (electrical)	Screw M10
Rated operating current max.	250 A
Rated operating voltage	690 V, 3~
For NH size	1
Note	The technical data may vary in the case of UR applications. UR applications only in conjunction with "Special Purpose Fuses".
Test specification	IEC 60 947-3 IEC 60 269-2 (fuse inserts)
Dimensions	Width: 184 mm Height: 298 mm Width: 7.24 " Height: 11.7 "
Connection of round conductors	10 - 150 mm <sup>2</sup>

# Features

---

Suitable for busbars	Height: 5, 10 mm Height: 0.2, 0.39 "
Number of poles	3-pole
Round conductor cross-section	10 - 150 mm <sup>2</sup>
Packaging unit	1 pc(s).
Net weight	2.258 kg
Gross weight	2.32 kg
Copper weight (kg per piece)	0.44
Customs tariff number	85369095
ETIM 9	EC000249
ECLASS 8.0	27371401
Product description	SV NH fuse-switch disconnecter, size 1, 250 A, 690 V , 3-pole, screw M10

# Approvals

---

Approvals	C-UR CQC-CCC UR + C-UR (recognized)
Explanations	Declaration of conformity Declaration of conformity UK