Rittal – The System.

Faster – better – everywhere.



SV 9343.210

NH Fuse-Switch Disconnectors

State: 11/11/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SV 9343.210 - NH Fuse-Switch Disconnectors

Features

Model No.	SV 9343.210
Version	For 60 mm busbar systems
Material	Polyamide Fire behavior corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated
Color	Chassis: RAL 7035 Cover: RAL 7035/7001
Clamping area for laminated copper bars:	Clamping area width: 50 mm Clamping area height: 10 mm Clamping area width: 1.97 ″ Clamping area height: 0.39 ″
For bar systems with center-to-center spacing	60 mm
Note	The technical data may vary in the case of UR applications. UR applications only in conjunction with "Special Purpose Fuses".
Cable outlet	Top/bottom
Type of connection (electrical)	Screw M10
Rated operating current max.	400 A
Rated operating voltage	690 V, 3~
For NH size	2
Test specification	IEC 60 947-3 IEC 60 269-2 (fuse inserts)
Dimensions	Width: 210 mm Height: 298 mm Width: 8.27 ″ Height: 11.7 ″
Connection of round conductors	10 - 240 mm²

© Rittal 2026

Features

Suitable for busbars	Height: 5, 10 mm Height: 0.2, 0.39 ″
Number of poles	3-pole
Round conductor cross-section	10 - 240 mm²
Packaging unit	1 pc(s).
Net weight	3.358 kg
Gross weight	3.36 kg
Copper weight (kg per piece)	1
Customs tariff number	85369095
ETIM 9	EC000249
ECLASS 8.0	27371401
Product description	SV NH fuse-switch disconnector, size 2, 400 A, 690 V, 3-pole, screw M10

Approvals

Approvals	C-UR CQC-CCC UR + C-UR (recognized)
Explanations	Declaration of conformity Declaration of conformity UK