

# Rittal – The System.

Faster – better – everywhere.



## SV 9343.300

## NH Fuse-Switch Disconnectors

State: 12/22/2025 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9343.300 - NH Fuse-Switch Disconnectors

## Features

Model No.	SV 9343.300
Material	Polyamide Fire behavior corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated
Color	Chassis: RAL 7035 Cover: RAL 7035/7001
Clamping area for laminated copper bars:	Clamping area width: 32 mm Clamping area height: 10 mm Clamping area width: 1.26 " Clamping area height: 0.39 "
Note	Connection of sector-shaped conductors 120 - 300 mm <sup>2</sup>
For bar systems with center-to-center spacing	60 mm
Cable outlet	Top/bottom
Type of connection (electrical)	Box terminal
Rated operating current max.	630 A
Rated operating voltage	690 V, 3~
For NH size	3
Note	The technical data may vary in the case of UR applications. UR applications only in conjunction with "Special Purpose Fuses".
Test specification	IEC 60 947-3 IEC 60 269-2 (fuse inserts)
Dimensions	Width: 250 mm Height: 298 mm Width: 9.84 " Height: 11.7 "
Connection of round conductors	95 - 300 mm <sup>2</sup>

# Features

Suitable for busbars	Height: 5, 10 mm Height: 0.2, 0.39 "
Clamping area for laminated copper bars:	20 mm 0.79 "
Number of poles	3-pole
Round conductor cross-section	95 - 300 mm <sup>2</sup>
Packaging unit	1 pc(s).
Net weight	4.48
Gross weight	4.5
Copper weight (kg per piece)	1.44
Customs tariff number	85369095
EAN	4028177540446
ETIM 9	EC000249
ECLASS 8.0	27371401

# Approvals

Approvals	C-UR CQC-CCC UR + C-UR (recognized)
Explanations	Declaration of conformity Declaration of conformity UK