

Rittal – The System.

Faster – better – everywhere.



SV 9393.233 Digital input module

State: 5/14/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9393.233 - Digital input module REM 800-DI 14

The digital input module expands the functionality of the REM 801 network analyzer with an additional 14 digital inputs.

Features

Model No.	SV 9393.233
Operating temperature range	-10 °C...55 °C 14 °F...131 °F
Storage temperature range	-25 °C...70 °C -13 °F...158 °F
Ambient humidity (non-condensing)	5...25 %
Contamination level	2
Counter frequency max.	20 Hz
Input signal low	0...5 V DC
Input signal high	18...28 V DC
Protection category IP to IEC 60529	IP 20
For support rail assembly	Yes
Connection of round conductors, fine wire without wire end ferrule	0.2 - 1.5 mm ²
Connection of round conductors, single-wire	0.2 - 1.5 mm ²
Connection of round conductors, multi-wire	0.2 - 1.5 mm ²
Connection for round conductor	AWG 16 - 24
Packaging unit	1 pc(s).
Net weight	0.29 kg
Gross weight	0.295 kg

Features

Customs tariff number	85389099
Product description	SV digital input module REM 800-DI 14

Approvals

Explanations	Declaration of conformity
--------------	---------------------------