Rittal – The System.

Faster – better – everywhere.



SV 9393.554
Current Transformers

State: 11/14/2026 (Source: www.rittal.com/us-en)

SV 9393.554 - Current Transformers

Features

Model No.	SV 9393.554
Version	Output voltage 333 mV
Material	Polyamide Fire behavior corresponding to UL 94
Color	RAL 9005
Supply includes	2x mounting feet 2 insulating caps 1 primary bar clamp 2 threaded pins
Suitable for busbars	40 x 12 2 x 30 x 10
Primary current	400 A
Standards	DIN EN 61869-1/2 EN 42600 VDE 0100 DIN EN 50274/VDE 0660-514 DGUV Regulation 3
Dimensions	Width: 60 mm Height: 80 mm Depth: 30 mm Width: 2.36 ″ Height: 3.15 ″ Depth: 1.18 ″
Operating temperature range	-5 °C...55 °C 23 °F...131 °F
Storage temperature range	-25 °C...75 °C -13 °F...167 °F
Ambient humidity (non-condensing)	10...90 %

© Rittal 2026

Features

Fundamental frequency	50...60 Hz
Accuracy Class	0.5
Insuslation material (class)	F
Packaging unit	1 pc(s).
Net weight	0.185 kg
Gross weight	0.194 kg
CRA risk class	Default (Low Risk)
Customs tariff number	85043129
ETIM 9	EC002048
Product description	SV Current transformer 400 A, 33 mm

Approvals

Explanations	Declaration of conformity