

Rittal – The System.

Faster – better – everywhere.



SV 9393.555 Current Transformers

State: 5/3/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9393.555 - Current Transformers

Features

| | |
|-----------------------------------|--|
| Model No. | SV 9393.555 |
| Version | Output voltage 333 mV |
| Material | Polyamide Fire behavior corresponding to UL 94 |
| Color | RAL 9005 |
| Supply includes | 2x mounting feet 2 insulating caps 1 primary bar clamp 2 threaded pins |
| Suitable for busbars | 2 x 50 x 10 |
| Primary current | 400 A |
| Standards | DIN EN 61869-1/2 EN 42600 VDE 0100 DIN EN 50274/VDE 0660-514 DGUV Regulation 3 |
| Dimensions | Width: 85 mm Height: 108 mm Depth: 30 mm Width: 3.35 " Height: 4.25 " Depth: 1.18 " |
| Operating temperature range | -5 °C...55 °C 23 °F...131 °F |
| Storage temperature range | -25 °C...75 °C -13 °F...167 °F |
| Ambient humidity (non-condensing) | 10...90 % |
| Fundamental frequency | 50...60 Hz |

Features

| | |
|-----------------------------|-------------------------------------|
| Accuracy Class | 0.5 |
| Insulation material (class) | F |
| Packaging unit | 1 pc(s). |
| Net weight | 0.3 kg |
| Gross weight | 0.309 kg |
| Customs tariff number | 85043129 |
| ETIM 9 | EC002048 |
| Product description | SV Current transformer 400 A, 52 mm |

Approvals

| | |
|--------------|---------------------------|
| Explanations | Declaration of conformity |
|--------------|---------------------------|