

Rittal – The System.

Faster – better – everywhere.



SV 9393.560 Current Transformers

State: 4/6/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9393.560 - Current Transformers

Features

Model No.	SV 9393.560
Version	Output voltage 333 mV
Material	Polyamide Fire behavior corresponding to UL 94
Color	RAL 9005
Supply includes	2x mounting feet 2 insulating caps 1 primary bar clamp 2 threaded pins
Suitable for busbars	80 x 15 2 x 60 x 10 3 x 50 x 10
Primary current	630 A
Standards	DIN EN 61869-1/2 EN 42600 VDE 0100 DIN EN 50274/VDE 0660-514 DGUV Regulation 3
Dimensions	Width: 105 mm Height: 132 mm Depth: 30 mm Width: 4.13 " Height: 5.2 " Depth: 1.18 "
Operating temperature range	-5 °C...55 °C 23 °F...131 °F
Storage temperature range	-25 °C...75 °C -13 °F...167 °F

Features

Ambient humidity (non-condensing)	10...90 %
Fundamental frequency	50...60 Hz
Accuracy Class	0.5
Insulation material (class)	F
Packaging unit	1 pc(s).
Net weight	0.295 kg
Gross weight	0.303 kg
Customs tariff number	85043129
ETIM 9	EC002048
Product description	SV Current transformer 630 A, 61 mm

Approvals

Explanations	Declaration of conformity
--------------	---------------------------