Rittal – The System.

Faster – better – everywhere.



SV 9393.565
Current Transformers

State: 11/15/2026 (Source: www.rittal.com/us-en)

SV 9393.565 - Current Transformers

Features

Model No.	SV 9393.565
Version	Output voltage 333 mV
Material	Polyamide Fire behavior corresponding to UL 94
Color	RAL 9005
Supply includes	2x mounting feet 2 insulating caps 1 primary bar clamp 2 threaded pins
Suitable for busbars	60 x 40 50 x 50
Primary current	1,250 A
Standards	DIN EN 61869-1/2 EN 42600 VDE 0100 DIN EN 50274/VDE 0660-514 DGUV Regulation 3
Dimensions	Width: 96 mm Height: 121 mm Depth: 30 mm Width: 3.78 ″ Height: 4.76 ″ Depth: 1.18 ″
Operating temperature range	-5 °C...55 °C 23 °F...131 °F
Storage temperature range	-25 °C...75 °C -13 °F...167 °F
Ambient humidity (non-condensing)	10...90 %

© Rittal 2026

Features

Fundamental frequency	50...60 Hz
Accuracy Class	0.5
Insuslation material (class)	F
Packaging unit	1 pc(s).
Net weight	0.3 kg
Gross weight	0.313 kg
Customs tariff number	85043129
ETIM 9	EC002048
Product description	SV Current transformer 1250 A, 61 mm

Approvals

Explanations	Declaration of conformity