

Rittal – The System.

Faster – better – everywhere.



SV 9345.015 Fuse Holders

State: 7/8/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9345.015 - Fuse Holders 31 A to 60 A

Fuse holder up to 60 A, 3-pole. Simple mounting on support rails or via OM component adapters.

Features

Model No.	SV 9345.015
Version	For fuse type class J
Material	Polyamide Fire protection corresponding to UL 94-V0
Color	RAL 7035
Connection for round conductor	AWG 1 - 18
Note	For snap-on mounting on 35 mm (7.5 mm/15 mm high) support rails to DIN EN 60 715 or RiLine component adapter combinations (OM adapters/supports)
Type of connection (electrical)	Box terminal
For fuse type (class)	J
Rated operating current max.	30 A
Rated operating voltage	600 V, 3~
Fuse standard	UL 248-8
Test specification	UL 4248-1 UL 4248-4 UL 4248-8
Dimensions	Width: 108 mm Height: 115 mm Width: 4.25 " Height: 4.53 "
Connection of round conductors	1.5 - 50 mm ²
Suitable for fuses	Diameter: 21 mm Length: 57 mm Diameter: 0.83 " Length: 2.24 "

Features

Voltage range for indicator lights	110 - 600 V
Electrical UL ratings (SCCR)	200 kA - 600 V, fuse class J max. 30 A, JDDZ/7
Number of poles	3-pole
Round conductor cross-section	1.5 - 50 mm ²
Packaging unit	2 pc(s).
Net weight	0.84 kg
Gross weight	0.966 kg
Copper weight (kg per piece)	0.072
Customs tariff number	85369095
ETIM 9	EC001644
ECLASS 8.0	27400613
Product description	SV Fuseholder, Class J, 30 A, 600 V, 3-pole, (60 mm)

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK