Rittal – The System.

Faster – better – everywhere.





KEL 9401.600 Ex Enclosures

State: 12/9/2025 (Source: rittal.com/us-en)



KEL 9401.600 - Ex Enclosures Stainless steel, empty enclosure with hinged door

Ex Housing with Hinged Door, Stainless Steel







Features

Model No.	KEL 9401.600
Version	Ex Enclosures
Applications	Zone 1 and 2 or 21 and 22 to 2014/34/EU Ambient temperature range: -30 °C+80 °C The specified temperatures can be limited by the installed equipment Explosion protection category to EN 60 079: Equipment protection due to increased safety (Ex e), equipment protection due to enclosure (Ex tb)
Material	Housing: Stainless steel 1.4301 (AISI 304) Door: Stainless steel 1.4301 (AISI 304), all-round foamed-in silicone seal Mounting plate: Carbon steel
Surface finish	Housing: Brushed, grain 400, peak-to-valley height < 0.8 μm Mounting panel: Zinc-plated
Supply includes	Housing Door Mounting panel

© Rittal 2025

Features

Dimensions	Width: 200 mm
	Height: 300 mm
	Depth: 155 mm
	Width: 7.87 "
	Height: 11.8 "
	Depth: 6.1 "
Dimensions of mounting plate (W	162 mm x 275 mm
x H)	6.38 ″ x 10.8 ″
Certificate IEC EX PTB 09.0035U	Yes
Certificate PTB 02 ATEX 1082U	Yes
Base material	Stainless steel 1.4301 (AISI 304)
Lock	Lock version: Cam
	No. of locks: 1
	Lock Insert: 3 mm double-bit
Protection category IP to IEC 60 529	IP 66
Protection category NEMA	NEMA 4X
Type rating according to UL 50E	Type 1
	Type 4
	Type 4X
	Type 12
Packaging unit	1 pc(s).
Net weight	4
Gross weight	4.28
Customs tariff number	94032080
EAN	4028177138681
ETIM 9	EC002503
ECLASS 8.0	27180502

Approvals

© Rittal 2025 3

Approvals

Approvals	ATEX
	ATEX QA
	CQC-CCC
	IECEx
	IECEx QAR
	UL + C-UL (listed)
Explanations	Attestation of Conformity

© Rittal 2025