

Rittal – The System.

Faster – better – everywhere.



KEL 9406.600 Ex Enclosures

State: 5/22/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



KEL 9406.600 - Ex Enclosures Stainless steel, empty enclosure with hinged door

Ex Housing with Hinged Door, Stainless Steel



Features

Model No.	KEL 9406.600
Version	Ex Enclosures
Applications	Zone 1 and 2 or 21 and 22 to 2014/34/EU Ambient temperature range: -30 °C...+80 °C The specified temperatures can be limited by the installed equipment Explosion protection category to EN 60 079: Equipment protection due to increased safety (Ex e), equipment protection due to enclosure (Ex tb)
Material	Housing: Stainless steel 1.4301 (AISI 304) Door: Stainless steel 1.4301 (AISI 304), all-round foamed-in silicone seal Mounting plate: Carbon steel
Surface finish	Housing: Brushed, grain 400, peak-to-valley height < 0.8 µm Mounting panel: Zinc-plated
Supply includes	Housing Door Mounting panel

Features

Dimensions	Width: 600 mm Height: 760 mm Depth: 210 mm Width: 23.6 " Height: 29.9 " Depth: 8.27 "
Dimensions of mounting plate (W x H)	549 mm x 730 mm 21.6 " x 28.7 "
Certificate IEC EX PTB 09.0035U	Yes
Certificate PTB 02 ATEX 1082U	Yes
Base material	Stainless steel 1.4301 (AISI 304)
Lock	Lock version: Cam No. of locks: 2 Lock Insert: 3 mm double-bit
Protection category IP to IEC 60 529	IP 66
Protection category NEMA	NEMA 4X
Type rating according to UL 50E	Type 1 Type 4 Type 4X Type 12
Packaging unit	1 pc(s).
Net weight	29.875 kg
Gross weight	30.38 kg
Customs tariff number	94032080
ETIM 9	EC002503
ECLASS 8.0	27180502
Product description	KEL Ex enclosure, WHD: 600x760x210 mm, Stainless steel 1.4301, with mounting plate, Empty enclosure with hinged door

Approvals

Approvals	ATEX ATEX QA CQC-CCC IECEX IECEX QAR UL + C-UL (listed)
-----------	--

Explanations	Attestation of Conformity
--------------	---------------------------