

Rittal – The System.

Faster – better – everywhere.



SV 9345.400 Fuse Holders

State: 7/14/2025 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9345.400 - Fuse Holders 61 A to 400 A

3-pole, for busbar systems with 60 mm bar center distance.

Features

Model No.	SV 9345.400
Version	For fuse type class J
Material	Polyamide Fire protection corresponding to UL 94-V0 Contact tracks: Electrolytic copper, silver-plated
Color	Chassis: RAL 7035 Cover: RAL 7035/7001
Connection for round conductor	AWG 4/0 – MCM 600
For bar systems with center-to-center spacing	60 mm
Cable outlet	Top/bottom
Type of connection (electrical)	Box terminal
For fuse type (class)	J
Rated operating current max.	400 A
Rated operating current (min.)	201 A
Rated operating voltage	600 V, 3~
Fuse standard	UL 248-8
Note	UL (listed accessory) is met through use of the fuse holder on RiLine busbar systems
Standards	UL 508
Dimensions	Width: 250 mm Height: 328 mm Width: 9.84 " Height: 12.9 "

Features

Suitable for fuses	Diameter: 54 mm Length: 181 mm Diameter: 2.13 " Length: 7.13 "
Suitable for busbars	Height: 5, 10 mm Height: 0.2, 0.39 "
Electrical UL ratings (SCCR)	100 kA - 600 V, fuse class J max. 400 A, JDDZ/7
Number of poles	3-pole
Packaging unit	1 pc(s).
Net weight	5
Gross weight	5.32
Copper weight (kg per piece)	2.106
Customs tariff number	85361090
EAN	4028177615670
ETIM 9	EC001644
ECLASS 8.0	27400613

Approvals

Approvals	C-UR UL + C-UL (listed) UR + C-UR (recognized)
-----------	--