

Rittal – The System.

Faster – better – everywhere.



SV 9345.614 Circuit-Breaker Component Adaptors

State: 6/10/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9345.614 - Circuit-Breaker Component Adaptors 4-pole

Features

| | |
|---|--|
| Model No. | SV 9345.614 |
| Material | Polyamide Fire protection corresponding to UL 94-V0 |
| Color | RAL 7035 |
| Supply includes | Connection straps Sliding Blocks |
| Rated current max. | 250 A |
| Rated operating voltage | 690 V, 4~ |
| Note | Cable outlet: Switch outlet or as outgoing cable from the switchgear The technical data may vary for UL applications. |
| Electrical UL ratings (SCCR) | 65 kA - 480 V, circuit breaker max. 250 A, DIVQ/7 |
| Cable outlet | Bottom |
| For bar systems with center-to-center spacing | 60 mm |
| Number of poles | 4-pole |
| Dimensions | Width: 140 mm Height: 310 mm Width: 5.51 " Height: 12.2 " |
| Suitable for busbars | Height: 5, 10 mm Height: 0.2, 0.39 " |
| To fit manufacturer (model) | ABB (T3S, XT3) Eaton (NZM2-4/250 A) Schneider Electric (NS(X)100, NS(X)160, NS(X)250) Schrack (MC2) Siemens (VL160X, VL160, VL250, 3RV10 63, 3VA12/20/21/22, 3VA61/62) |
| Packaging unit | 1 pc(s). |

Features

| | |
|------------------------------|---|
| Net weight | 2.405 kg |
| Gross weight | 2.526 kg |
| Copper weight (kg per piece) | 1.134 |
| Customs tariff number | 85369095 |
| ETIM 9 | EC001531 |
| ECLASS 8.0 | 27370304 |
| Product description | SV Circuit-breaker component adaptor, 250 A, 690 V, 4-pole, cable outlet bottom, with connection straps |

Approvals

| | |
|--------------|---|
| Approvals | ABS DNV Lloyds Register |
| Explanations | Declaration of conformity Declaration of conformity UK |