

Rittal – The System.

Faster – better – everywhere.



RX 9360.000

RiLineX baying set

State: 8/9/2025 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.000 - RiLineX baying set for board

RiLineX baying connector set for the complete board, for use with 550 A and 800 A. Comprising a busbar connector and contact hazard protection cover. For simple baying of boards between two bayed VX enclosures, no drilling required.

Features

Model No.	RX 9360.000
Benefits	Time saving through complete digital product data Shorter mounting time thanks to pre-mounted complete board Tested short circuit resistance up to max. 65 kA Suitable for applications in the alternating current range up to 1,000 V AC and direct current up to 1,500 V DC Contact hazard protection up to IP 2XB, can be upgraded to IP 4X Tested and certified to IEC and UL Simple extension and baying
Material	Upper part: carbon steel, zinc-plated Contact plate: E-Cu, tin-plated Front cover: polyamide (PA 6) Fire behavior corresponding to UL 94
Color	RAL 35745
Supply includes	3 rail connectors 1 front cover 1 insulating plate
Protection category IP to IEC 60 529	IP 2XB
Standards	IEC 61 439-1/-2 UL 508
Rated current max.	780 A
Rated current (UL)	780 A

Features

Electrical UL ratings (SCCR)	52.5 kA - 600 V, RMS 100 kA - 600 V, fuse class L max. 1600 A, JDDZ/7 100 kA - 600 V, circuit breaker max. 600 A, DIVQ/7 100 kA - 480 V, circuit breaker max. 800 A, DIVQ/7 65 kA - 600 V, circuit breaker max. 800 A, DIVQ/7
Rated impulse withstand voltage U _{Imp}	12 kV
Rated voltage	1,000 V AC 1,500 V DC 600 V AC (UL) 600 V DC (UL)
Rated insulation voltage	1,000 V AC 1,500 V DC
Rated impulse withstand current	103 kA 115.5 kA
Rated short-time withstand current/t	45 kA/200 ms 52.5 kA/500 ms
Overvoltage category	4
Contamination level	3
Number of poles	3-pole
Fundamental frequency	50...60 Hz
Ambient humidity (non- condensing)	10...90 %
Suitable for busbars	30 x 5/10
Operating temperature range	-5 °C...55 °C 23 °F...131 °F
Dimensions	Width: 153 mm Height: 240 mm Depth: 77 mm Width: 6.02 " Height: 9.45 " Depth: 3.03 "
Packaging unit	1 pc(s).

Features

Net weight	1.88
Gross weight	1.924
Copper weight (kg per piece)	0.297
Customs tariff number	85369010
EAN	4028177997431
ETIM 9	EC002270

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity