


**Rittal – The System.**

Faster – better – everywhere.



**RX 9360.008**

**RiLineX Board**

State: 2/13/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE




SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# RX 9360.008 - RiLineX Board

Complete board 800 A, 905 mm for 1,000-mm-wide enclosures.



## Features

Model No.	RX 9360.008
Benefits	<p>Time saving through complete digital product data</p> <p>Shorter mounting time thanks to pre-mounted complete board</p> <p>Suitable for applications in the alternating current range up to 1,000 V AC and direct current up to 1,500 V DC</p> <p>Tested short circuit resistance up to max. 65 kA</p> <p>Contact hazard protection up to IP 2XB, can be upgraded to IP 3X</p> <p>Tested and certified according to IEC and UL</p> <p>Simple expansion and field alignment</p>
Material	<p>Polyamide (PA 6)</p> <p>Fire behavior corresponding to UL 94</p> <p>E-Cu</p>
Color	<p>RAL 35745</p> <p>RAL 9005</p>
Supply includes	Including integrated busbars
Protection category IP to IEC 60 529	IP 2XB
Standards	<p>IEC 61 439-1/-2</p> <p>UL 508</p>
Rated current max.	800 A

# Features

Rated current (UL)	800 A
Electrical UL ratings (SCCR)	65 kA - 600 V, RMS, unprotected 100 kA - 600 V, fuse class L max. 1600 A, JDDZ/7 100 kA - 600 V, circuit breaker max. 600 A, DIVQ/7 100 kA - 480 V, circuit breaker max. 800 A, DIVQ/7 65 kA - 600 V, circuit breaker max. 800 A, DIVQ/7
Center-to-center spacing of busbars	60 mm
Rated impulse withstand voltage UImp	12 kV
Rated voltage	1,000 V AC 1,500 V DC 600 V AC (UL) 600 V DC (UL)
Rated insulation voltage Ui	1,000 V AC 1,500 V DC
Rated impulse withstand current	143 kA 143 kA (UL)
Rated short-time withstand current/t	65 kA/500 ms
Overvoltage category	4
Contamination level	3
Busbar dimensions	30 mm x 10 mm 1.18 " x 0.39 "
Number of poles	3-pole
Fundamental frequency	50...60 Hz
Ambient humidity (non-condensing)	10...90 %
Operating temperature range	-5 °C...55 °C 23 °F...131 °F
Storage temperature range	-25 °C...75 °C -13 °F...167 °F

## Features

---

Dimensions	Width: 905 mm Height: 246 mm Depth: 49.2 mm Width: 35.6 " Height: 9.69 " Depth: 1.94 "
Packaging unit	1 pc(s).
Net weight	11.5
Gross weight	12.032
Copper weight (kg per piece)	7.224
Customs tariff number	85369010
EAN	4028177997417
ETIM 9	EC001900

---

## Approvals

---

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity

---