Rittal – The System.

Faster – better – everywhere.



SV 9635.371

Component Adapters

State: 11/19/2026 (Source: www.rittal.com/us-en)

SV 9635.371 - Component Adapters 1-pole

For assembly of switchgear and protective devices.

Features

Model No.	SV 9635.371
Version	L1
Function principle	For mechanical attachment and direct contacting of electrical equipment on the board
Material	Polyamide Fire behavior corresponding to UL 94
Color	RAL 7035
Note	Different adapter designs are required depending on the desired phase connection The technical data may vary for UL applications.
Rated current max.	16 A
Rated operating voltage	690 V (AC), 1~
Number of poles	1-pole
Connection cables (AWG)	AWG 14
Length of connection cable	100 mm 3.94 ″
Support rails Qty/height	1 / 10 mm 0.39 ″
Support rail type	Fixed
Dimensions	Width: 18 mm Height: 160 mm Depth: 35 mm Width: 0.71 ″ Height: 6.3 ″ Depth: 1.38 ″
Packaging unit	6 pc(s).

© Rittal 2026

Features

Net weight	0.3 kg
Gross weight	0.358 kg
Copper weight (kg per piece)	0.006
Customs tariff number	85369095
ETIM 9	EC001531
ECLASS 8.0	27370304
Product description	SV component adaptor 16 A, 690 V (AC), 1-pole (variant L1), connection cable AWG 14, WH: 18 x 160 mm

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK

© Rittal 2026