Rittal – The System.

Faster – better – everywhere.



# SV 9635.372

# Component Adapters

State: 11/14/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# SV 9635.372 - Component Adapters 1-pole

For assembly of switchgear and protective devices.

## Features

| | |
|---|---|
| Model No. | SV 9635.372 |
| Version | L2 |
| Function principle | For mechanical attachment and direct contacting of electrical equipment on the board |
| Material | Polyamide<br>Fire behavior corresponding to UL 94 |
| Color | RAL 7035 |
| Note | Different adapter designs are required depending on the desired phase connection<br>The technical data may vary for UL applications. |
| Rated current max. | 16 A |
| Rated operating voltage | 690 V (AC), 1~ |
| Number of poles | 1-pole |
| Connection cables (AWG) | AWG 14 |
| Length of connection cable | 100 mm<br>3.94 ″ |
| Support rails Qty/height | 1 / 10 mm<br>0.39 ″ |
| Support rail type | Fixed |
| Dimensions | Width: 18 mm<br>Height: 160 mm<br>Depth: 35 mm<br>Width: 0.71 ″<br>Height: 6.3 ″<br>Depth: 1.38 ″ |
| Packaging unit | 6 pc(s). |

© Rittal 2026

# Features

| | |
|---|---|
| Net weight | 0.33 kg |
| Gross weight | 0.373 kg |
| Copper weight (kg per piece) | 0.008 |
| Customs tariff number | 85369095 |
| ETIM 9 | EC001531 |
| ECLASS 8.0 | 27370304 |
| Product description | SV component adaptor 16 A, 690 V (AC), 1-pole (variant L2), connection cable AWG 14, WH: 18 x 160 mm |

# Approvals

| | |
|---|---|
| Approvals | UL + C-UL (listed) |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |

© Rittal 2026