

**Rittal – The System.**

Faster – better – everywhere.



**RX 9360.110**

**RiLineX basic module**

State: 2/4/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))



FRIEDHELM LOH GROUP

# RX 9360.110 - RiLineX basic module

Board module, 3-pole, 100 mm wide, incl. busbar support and contact hazard protection cover



## Features

Model No.	RX 9360.110
Benefits	<p>Scalable system lengths with basic modules</p> <p>Easy mounting</p> <p>Scalable rated currents due to variable busbar cross-sections</p> <p>Tested short circuit resistance up to max. 65 kA</p> <p>Suitable for applications in the alternating current range up to 1,000 V AC and direct current up to 1,500 V DC</p> <p>Contact hazard protection up to IP 2XB, can be upgraded to IP 3X</p> <p>Tested and certified according to IEC and UL</p> <p>Simple expansion and field alignment</p>
Material	<p>Polyamide (PA 6)</p> <p>Fire behavior corresponding to UL 94</p>
Color	<p>RAL 35745</p> <p>RAL 9005</p>
Supply includes	<p>Base module lower part</p> <p>Base module (contact hazard protection cover)</p> <p>Assembly screws</p>
Protection category IP to IEC 60 529	IP 2XB
Standards	<p>IEC/EN 61439-1</p> <p>UL 508</p>

# Features

Rated current max.	800 A
Note	Busbars are not included with the supply
Electrical UL ratings (SCCR)	65 kA - 600 V, RMS, unprotected 100 kA - 600 V, fuse class L max. 1600 A, JDDZ/7 100 kA - 480 V, circuit breaker max. 800 A, DIVQ/7 65 kA - 600 V, circuit breaker max. 800 A, DIVQ/7
Center-to-center spacing of busbars	60 mm
Rated impulse withstand voltage Ulmp	12 kV
Rated voltage	1,000 V AC 600 V AC (UL) 1,500 V DC 600 V DC (UL)
Rated insulation voltage	1,000 V AC 1,500 V DC
Rated short-time withstand current/t	65 kA/500 ms
Overvoltage category	4
Contamination level	3
Number of poles	3-pole
Fundamental frequency	50...60 Hz
Ambient humidity (non-condensing)	10...90 %
Suitable for busbars	15 x 5/10 20 x 5/10 30 x 5/10
Operating temperature range	-5 °C...55 °C 23 °F...131 °F
Storage temperature range	-25 °C...75 °C -13 °F...167 °F

# Features

---

Dimensions	Width: 100 mm Height: 246 mm Depth: 49.2 mm Width: 3.94 " Height: 9.69 " Depth: 1.94 "
Packaging unit	6 pc(s).
Net weight	3
Gross weight	3.292
Customs tariff number	85369010
EAN	4028177997295
ETIM 9	EC001900

# Approvals

---

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity