

Rittal – The System.

Faster – better – everywhere.



RX 9360.200

RiLineX connection adapter

State: 6/1/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.200 - RiLineX connection adapter

Connection adapter RiLineX busbar platform for snap-on mounting, push-in conductor connection. Semi-automatic adjustment of busbar thickness 5/10 mm.



Features

Model No.	RX 9360.200
Benefits	Easy mounting
Material	Polyamide (PA 6) Fire behavior corresponding to UL 94
Color	RAL 9005
Rated current (reference value, IEC)	67 A
Rated current of round conductor max.(IEC)	76 A
Rated current of round conductor max. (UL)	66 A
Electrical UL ratings (SCCR)	5 kA - 600 V, RMS, unprotected 35 kA - 480 V, circuit breaker max. 60 A, DIVQ/7 100 kA - 600 V, fuse class J max. 100 A, JDDZ/7
Cable outlet	Top/bottom
For bar systems with center-to-center spacing	60 mm
Number of poles	3-pole

Features

Suitable for busbar system	RiLineX RiLine60
Dimensions	Width: 26.8 mm Height: 239.2 mm Depth: 103.3 mm Width: 1.06 " Height: 9.42 " Depth: 4.07 "
Connection of round conductors	1.5 - 16 mm ²
Suitable for busbars	12 x 5/10 15 x 5/10 20 x 5/10 30 x 5/10
Rated voltage	800 V AC 800 V DC 600 V AC (UL) 600 V DC (UL)
Overvoltage category	4
Contamination level	3
Standards	IEC/EN 61439-1 UL 508
Rated impulse withstand voltage U _{Imp}	8 kV
Rated insulation voltage U _i	800 V
Power loss max.	7 W 24 BTU/h
Protection category IP to IEC 60 529	IP 2X
Maximum operating air humidity	90 %
Operating temperature range	-5 °C...55 °C 23 °F...131 °F
Storage temperature range	-25 °C...75 °C -13 °F...167 °F

Features

Ambient humidity (non-condensing)	10...90 %
For busbar thickness	5 - 10 mm 0.2 - 0.39 "
Packaging unit	4 pc(s).
Net weight	1.2 kg
Gross weight	1.656 kg
PCF/VE (cradle-to-gate)	13.4
Customs tariff number	85369010
ETIM 9	EC001531
Product description	RX connection adapter 3-pole, WH: 27x240 mm, conductor connection max. 16 mm ²

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity PCF-declaration
