## Rittal – The System.

Faster – better – everywhere.





# SV 9635.381 Component Adapters

State: 11/7/2025 (Source: rittal.com/us-en)



# SV 9635.381 - Component Adapters 1-pole

For assembly of switchgear and protective devices.

#### **Features**

Model No.	SV 9635.381
Version	L1
Function principle	For mechanical attachment and direct contacting of electrical equipment on the board
Material	Polyamide Fire behavior corresponding to UL 94
Color	RAL 7035
Note	Different adapter designs are required depending on the desired phase connection The technical data may vary for UL applications.
Rated current max.	63 A
Rated operating voltage	690 V (AC), 1~
Number of poles	1-pole
Connection cables (AWG)	AWG 8
Length of connection cable	100 mm 3.94 ″
Support rails Qty/height	1 / 10 mm 0.39 ″
Support rail type	Fixed
Dimensions	Width: 18 mm Height: 160 mm Depth: 35 mm Width: 0.71 " Height: 6.3 " Depth: 1.38 "
Packaging unit	6 pc(s).

© Rittal 2025

### Features

Net weight	0.33
Gross weight	0.425
Copper weight (kg per piece)	0.015
Customs tariff number	85369095
EAN	4028177934535
ETIM 9	EC001531
ECLASS 8.0	27370304

# **Approvals**

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3