

Rittal – The System.

Faster – better – everywhere.



RX 9360.513

RiLineX Circuit-breaker component adaptor

State: 8/3/2025 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.513 - RiLineX Circuit-breaker component adaptor

CB component adaptors for the RiLineX busbar platform in widths 81 to 140 mm. For mounting moulded-case circuit-breakers (MCCBs). Products are available in two variants: An "Easy-Fix" variant for user-friendly external mounting of switches from all standard manufacturers, and a "Universal" variant with U nuts for maximum flexibility.

Features

Model No.	RX 9360.513
Version	Easy Fix
Benefits	Direct mounting of compact circuit breaker MCCB on the board Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm Fast, simple pre-assembly of standard market switch types outside of the enclosure
Material	Polyamide (PA 6) Fire behavior corresponding to UL 94
Color	RAL 9005 RAL 35745
Protection category IP to IEC 60 529	IP 2XB
Rated current max.	250 A
Rated current (UL)	210 A
Rated impulse withstand voltage U _{Imp}	12 kV
Rated voltage	690 V AC 690 V DC 600 V AC (UL)
Rated insulation voltage	1,000 V
Overvoltage category	4
Contamination level	3
Number of poles	3-pole

Features

Cable outlet	Top
Type of connection (electrical)	Screw M8
Suitable for busbar system	RiLineX RiLine60
Fundamental frequency	50...60 Hz
Ambient humidity (non-condensing)	10...90 %
Suitable for busbars	15 x 5/10 20 x 5/10 30 x 5/10
Operating temperature range	-25 °C...55 °C -13 °F...131 °F
Storage temperature range	-25 °C...75 °C -13 °F...167 °F
Dimensions	Width: 105 mm Height: 252 mm Depth: 63 mm Width: 4.13 " Height: 9.92 " Depth: 2.48 "
Packaging unit	1 pc(s).

Approvals

Approvals	UL + C-UL (listed)
-----------	--------------------