Rittal – The System.

Faster - better - everywhere.





SV 9635.400 Motor control unit

State: 11/11/2025 (Source: rittal.com/us-en)



SV 9635.400 - Motor control unit 3-pole

For controlling motors as direct or reversing starter with integral overload protection.

Features

Model No.	SV 9635.400
Function principle	For controlling motors as direct or reversing starter with integral
	overload protection
	The hybrid technology used allows for frequent switching with no
	wear by means of semiconductors
	During operation, mechanical contacts ensure low power loss
	Space-saving design due to low structural width
Material	Polyamide
	Fire protection corresponding to UL 94-V0
Color	RAL 7035
Power dissipation (max.)	2.8 W
	10 BTU/h
Rated operating voltage	500 V (AC), 3~, 50 Hz/60 Hz
Rated current max.	0.6 A
Note	The technical data may vary for UL applications.
Dimensions	Width: 22.5 mm
	Height: 160 mm
	Depth: 114 mm
	Width: 0.89 "
	Height: 6.3 "
	Depth: 4.49 "
Connection of round conductors	0.14 - 2.5 mm²
Adjustable current monitoring	0.075 - 0.6 A
Packaging unit	1 pc(s).
Net weight	0.38
Gross weight	0.389
Customs tariff number	85371091

© Rittal 2025

Features

EAN	4028177817319
ETIM 9	EC002572
ECLASS 8.0	27370804

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity

© Rittal 2025 3