

Rittal – The System.

Faster – better – everywhere.



RX 9360.525

RiLineX CB device adapter


State: 2/14/2026 (Source: ittal.com/us-en)



FRIEDHELM LOH GROUP

RX 9360.525 - RiLineX CB device adapter

RiLineX CB device adapter (3-pole, max. 400 A) for 60 mm busbar systems. Device width 145 mm. Thanks to the Easy-Fix concept, adapter and switch installation can be carried out independently of each other. This concept is available for all popular manufacturers. The adapter has tool-free snap-on mounting with semi-automatic adjustment of the rail thickness between 5 and 10 mm. The cable outlet can be adapted to individual requirements by simply converting the outlet at the bottom or top.



Features

Model No.	RX 9360.525
Version	Easy Fix
Benefits	Direct mounting of compact circuit breaker MCCB on the board Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm Quick and easy pre-assembly of standard switch types outside the control cabinet
Material	Polyamide (PA 6) Fire behavior corresponding to UL 94
Color	RAL 9005 RAL 35745
Supply includes	Incl. 3 clamp covers
Protection category IP to IEC 60529	IP 2XB

Features

Rated impulse withstand voltage UImp	12 kV
Rated voltage	690 V AC 690 V DC 600 V AC (UL)
Rated insulation voltage Ui	1,000 V
Overvoltage category	4
Contamination level	3
Clamping area for laminated copper bars (W x H)	29 x 6 mm 1.14 x 0.24 "
Number of poles	3-pole
Cable outlet	Top/bottom
Type of connection (electrical)	Screw M10
To fit manufacturer (model)	Our selection aid, available in the Downloads section, helps you to easily find a matching component adaptor.
Suitable for busbar system	RiLineX RiLine60
Fundamental frequency	50...60 Hz
Ambient humidity (non-condensing)	10...90 %
Suitable for busbars	15 x 5/10 20 x 5/10 30 x 5/10
Operating temperature range	-25 °C...55 °C -13 °F...131 °F
Storage temperature range	-25 °C...75 °C -13 °F...167 °F
Dimensions	Width: 145 mm Height: 325.8 mm Width: 5.71 " Height: 12.8 "
Packaging unit	1 pc(s).

Features

Net weight	4
Gross weight	4.298
Copper weight (kg per piece)	1.652
Customs tariff number	85369095
EAN	4028177997127
ETIM 9	EC001531

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity
