


Rittal – The System.

Faster – better – everywhere.



SV 9635.410

Motor control unit

State: 1/14/2026 (Source: ittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9635.410 - Motor control unit 3-pole

For controlling motors as direct or reversing starter with integral overload protection.

Features

Model No.	SV 9635.410
Function principle	<p>For controlling motors as direct or reversing starter with integral overload protection</p> <p>The hybrid technology used allows for frequent switching with no wear by means of semiconductors</p> <p>During operation, mechanical contacts ensure low power loss</p> <p>Space-saving design due to low structural width</p>
Material	Polyamide Fire protection corresponding to UL 94-V0
Color	RAL 7035
Power dissipation (max.)	5.5 W 19 BTU/h
Rated operating voltage	500 V (AC), 3~, 50 Hz/60 Hz
Rated current max.	2.4 A
Note	The technical data may vary for UL applications.
Dimensions	Width: 22.5 mm Height: 160 mm Depth: 114 mm Width: 0.89 " Height: 6.3 " Depth: 4.49 "
Connection of round conductors	0.14 - 2.5 mm ²
Adjustable current monitoring	0.18 - 2.4 A
Packaging unit	1 pc(s).
Net weight	0.38
Gross weight	0.387
Customs tariff number	85371091

Features

EAN 4028177817302

ETIM 9 EC002572

ECLASS 8.0 27370804

Approvals

Approvals UL + C-UL (listed)

Explanations Declaration of conformity