
Rittal – The System.

Faster – better – everywhere.



RX 9360.600

RiLineX CB device adapter


State: 11/5/2026 (Source: www.rittal.com/us-en)

RX 9360.600 - RiLineX CB device adapter

CB device adapter (3-pole, max. 160 A) for the RiLineX busbar platform and 60 mm busbar systems such as RiLine60. The device width on the busbar system is 81 mm. The "universal" version with sliding nuts offers maximum flexibility for switch installation. The adapter has tool-free snap-on mounting with semi-automatic adjustment of the rail thickness between 5 and 10 mm. Version for cable outlet at the bottom.







Features

Model No.	RX 9360.600
Version	universal IMPORTANT: Only suitable for MCCBs with box terminals!
Benefits	Direct mounting of compact circuit breaker MCCB on the board Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm Quick and easy pre-assembly of standard switch types outside the control cabinet
Material	Polyamide (PA 6) Fire behavior corresponding to UL 94
Color	RAL 9005 RAL 35745
Supply includes	Incl. 3 connection compartment covers
Protection category IP to IEC 60 529	IP 2XB
Rated current (UL)	400 A

Features

Electrical UL ratings (SCCR)	65 kA - 480 V, circuit breaker max. 125 A, DIVQ/7
Rated impulse withstand voltage UImp	8 kV
Rated voltage	690 V AC 600 VAC(UL)
Rated insulation voltage Ui	1,000 V
Contamination level	3
Number of poles	3-pole
Cable outlet	Bottom
Type of connection (electrical)	Box terminal
Cross-section	9 mm² 6 mm²
To fit manufacturer (model)	Easily find the right device adapter with our selection guide in the Downloads area.
Suitable for busbar system	RiLineX RiLine60
Power loss max.	8 W 27 BTU/h
Fundamental frequency	50...60 Hz
Ambient humidity (non-condensing)	10...90 %
Suitable for busbars	15 x 5/10 20 x 5/10 30 x 5/10
Operating temperature range	-25 °C...55 °C -13 °F...131 °F
Storage temperature range	-25 °C...75 °C -13 °F...167 °F

Features

Dimensions	Width: 82 mm Height: 251.4 mm Depth: 50.8 mm Width: 3.23 ″ Height: 9.9 ″ Depth: 2 ″
Fire load	22.045 MJ/m²
Packaging unit	1 pc(s).
Net weight	0.92 kg
Gross weight	1.22 kg
Copper weight (kg per piece)	0.375
PCF/VE (cradle-to-gate)	12.73
Customs tariff number	85369095
ETIM 9	EC001531
Product description	RX CB device adapter 160 A, 3-pole, version: Universal Fix, cable outlet at bottom, W: 81 mm

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity PCF-declaration