

Rittal – The System.

Faster – better – everywhere.



SV 9661.050

Baying Bracket E-Cu

State: 6/9/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9661.050 - Baying Bracket E-Cu

The PE/PEN combination, consisting of busbars, combination angles and baying brackets, supports type-tested configurations as per IEC 61 439-1.

Features

Model No.	SV 9661.050
Product description	To join flat busbars from enclosure to enclosure in combination with PE/PEN combination angle.
Material	E-Cu
Suitable for busbars	Busbar E-Cu with integral punchings
Dimensions	Length: 88 mm Length: 3.46 "
Suitable for busbars	Width: 40 Height: 10 mm Width: 1.57 Height: 0.39 "
Packaging unit	4 pc(s).
Net weight	1.6 kg
Gross weight	1.823 kg
Copper weight (kg per piece)	0.28
Customs tariff number	74198090
ETIM 9	EC002270
ECLASS 8.0	27409221
Product description	SV Baying bracket E-Cu, L: 88 mm, for E-Cu 40x10 mm

Approvals

Approvals

Explanations

Declaration of conformity

Declaration of conformity UK