

Rittal – The System.

Faster – better – everywhere.



RX 9360.720

RiLineX device adapter

State: 4/7/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE



SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.720 - RiLineX device adapter

Component adapter 45 mm. Snap-on mounting of components.



Features

Model No.	RX 9360.720
Version	With connection cable
Benefits	For mounting equipment for top-hat rail mounting, e.g. motor starter Pre-assembled connection cable Simple connector lock for component support rails Optional component anti-slip guard Snap-on mounting and easy adjustment on busbar thickness 5/10 mm Easy mounting Reduction of article variety through coordinated accessories
Material	Polyamide (PA 6) Fire behavior corresponding to UL 94
Color	RAL 9005 RAL 35745
Connection cables (AWG)	AWG 12
Rated current (max.)	25 A
Rated current of round conductor	25 A
Rated current round conductor (UL)	25 A

Features

Electrical UL ratings (SCCR)	5 kA - 600 V, RMS, unprotected 100 kA - 600 V, fuse class RK5 max. 30 A, JDDZ/7 50 kA - 480 V, circuit breaker max. 22 A, DIVQ/7 65 kA - 480 V, Combination Motor Controller max. 16 A, NKJH/7 30 kA - 600 V, Combination Motor Controller max. 12.5 A, NKJH/7 65 kA - 480 V, Combination Motor Controller max. 40 A, NKJH/7
Cable outlet	Top
For bar systems with center-to-center spacing	60 mm
Length of connection cable	160 mm 6.3 "
Number of poles	3-pole
Suitable for busbar system	RiLineX RiLine60
Dimensions	Width: 45 mm Height: 239.4 mm Depth: 36.2 mm Width: 1.77 " Height: 9.43 " Depth: 1.43 "
Support rails Qty/height	1 / 10 mm 0.39 "
Suitable for busbars	15 x 5/10 20 x 5/10 30 x 5/10
Rated voltage	690 V AC 600 V AC (UL) 600 V DC (UL)
Overvoltage category	4
Contamination level	3
Standards	IEC 61 439-1/-2 UL 508
Protection category IP to IEC 60529	IP 2XB

Features

Maximum operating air humidity	90 %
Operating temperature range	-5 °C...55 °C 23 °F...131 °F
Storage temperature range	-25 °C...75 °C -13 °F...167 °F
Ambient humidity (non-condensing)	10...90 %
Packaging unit	4 pc(s).
Net weight	1.36 kg
Gross weight	1.39 kg
Copper weight (kg per piece)	0.096
Customs tariff number	85369095
ETIM 9	EC001531
Product description	RX component adapter 25 A, AWG 12, 3-pole, W: 45 mm

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity PCF-declaration
