

Rittal – The System.

Faster – better – everywhere.



SV 9661.230

PE/PEN Combination Angle, E-Cu

State: 12/20/2025 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9661.230 - PE/PEN Combination Angle, E-Cu for PE/PEN combinations

The PE/PEN combination, comprising busbars, combination angles and baying brackets, supports type-tested configurations as per IEC 61 439-1.

Features

Model No.	SV 9661.230
Product description	The PE/PEN combination, comprising busbars, combination angles and baying brackets, supports type-tested configurations as per IEC 61 439-1.
Benefits	The pre-assembled combination angles, baying brackets and the busbars individually cut to the enclosure width make for extremely time and cost-efficient assembly
Applications	Form 2-4 Others
Material	E-Cu
Supply includes	Assembly components
Approved short-circuit current capability	I _{cw} 30 kA, 1 sec.
Suitable for busbars	Busbar E-Cu with integral punchings
OUT_CROSS_SECTION_COL_SM	30 - 10 mm 1.18 - 0.39 ~
Suitable for busbars	Width: 30 Height: 10 mm Width: 1.18 Height: 0.39 ~
Packaging unit	4 pc(s).
Net weight	2
Gross weight	2.177
Copper weight (kg per piece)	0.408

Features

Customs tariff number	74198090
EAN	4028177546653
ETIM 9	EC000329
ECLASS 8.0	27400605

Approvals

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---