

**Rittal – The System.**

Faster – better – everywhere.



**RX 9360.730**

**RiLineX device adapter**

State: 1/25/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# RX 9360.730 - RiLineX device adapter

Component adapter 45 mm. Snap-on mounting of components.



## Features

|   |   |
|---|---|
| Model No.                                     | RX 9360.730   |
| Version                                       | With connection cable   |
| Benefits                                      | <p>For mounting equipment for top-hat rail mounting, e.g. motor starter</p> <p>Pre-assembled connection cable AWG 14 - 2 (16 A - 100 A)</p> <p>Simple connector lock for component support rails</p> <p>Optional component anti-slip guard</p> <p>Snap-on mounting and easy adjustment on busbar thickness 5/10 mm</p> <p>Easy mounting</p> <p>Reduction of article variety through coordinated accessories</p> |
| Material                                      | <p>Polyamide (PA 6)</p> <p>Fire behavior corresponding to UL 94</p>   |
| Color   | <p>RAL 9005</p> <p>RAL 35745</p>  |
| Connection cables (AWG)                       | AWG 10  |
| Rated current of round conductor              | 40 A  |
| Rated current of round conductor (UL)         | 40 A  |
| Cable outlet                                  | Top   |
| For bar systems with center-to-center spacing | 60 mm   |

# Features

|                                      |  |
|--------------------------------------|--|
| Length of connection cable           | 160 mm<br>6.3 "  |
| Number of poles                      | 3-pole   |
| Suitable for busbar system           | RiLineX<br>RiLine60  |
| Dimensions                           | Width: 45 mm<br>Height: 239.4 mm<br>Depth: 36.2 mm<br>Width: 1.77 "<br>Height: 9.43 "<br>Depth: 1.43 " |
| Support rails Qty/height             | 1 / 10 mm<br>0.39 "  |
| Suitable for busbars                 | 15 x 5/10<br>20 x 5/10<br>30 x 5/10  |
| Rated voltage                        | 690 V AC<br>600 V AC (UL)<br>600 V DC (UL)   |
| Overvoltage category                 | 4  |
| Contamination level                  | 3  |
| Standards                            | IEC 61 439-1/-2<br>UL 508  |
| Protection category IP to IEC 60 529 | IP 2XB   |
| Operation humidity max               | 90 %   |
| Operating temperature range          | -5 °C...55 °C<br>23 °F...131 °F  |
| Storage temperature range            | -25 °C...75 °C<br>-13 °F...167 °F  |
| Ambient humidity (non-condensing)    | 10...90 %  |
| Packaging unit                       | 4 pc(s).   |

## Features

---

|                              |               |
|------------------------------|---------------|
| Net weight                   | 1.42          |
| Gross weight                 | 1.45          |
| Copper weight (kg per piece) | 0.088         |
| Customs tariff number        | 85369095      |
| EAN                          | 4028177997011 |
| ETIM 9                       | EC001531      |

---

## Approvals

---

|              |                           |
|--------------|---------------------------|
| Approvals    | UL + C-UL (listed)        |
| Explanations | Declaration of conformity |

---