
Rittal – The System.

Faster – better – everywhere.





SV 9661.235 PE/PEN Combination Angle, E-Cu

State: 11/3/2025 (Source: rittal.com/us-en)



SV 9661.235 - PE/PEN Combination Angle, E-Cu for PE/PEN combinations

The PE/PEN combination, comprising busbars, combination angles and baying brackets, supports type-tested configurations as per IEC 61 439-1.

Features

Model No.	SV 9661.235
Product description	The PE/PEN combination, comprising busbars, combination angles and baying brackets, supports type-tested configurations as per IEC 61 439-1.
Benefits	The pre-assembled combination angles, baying brackets and the busbars individually cut to the enclosure width make for extremely time and cost-efficient assembly
Applications	Form 2-4 Others
Material	E-Cu
Supply includes	Assembly components
Approved short-circuit current capability	Icw 18 kA, 1 sec.
Suitable for busbars	Busbar E-Cu with integral punchings
OUT_CROSS_SECTION_COL_SM	30 - 5 mm 1.18 - 0.2 ″
Suitable for busbars	Width: 30 Height: 5 mm Width: 1.18 Height: 0.2 "
Packaging unit	4 pc(s).
Net weight	1.156
Gross weight	1.256
Copper weight (kg per piece)	0.2

© Rittal 2025 2

Features

Customs tariff number	74198090
EAN	4028177546677
ETIM 9	EC000329
ECLASS 8.0	27400605

Approvals

Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3