


Rittal – The System.

Faster – better – everywhere.



RX 9360.760

RiLineX device adapter

State: 5/24/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE



SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.760 - RiLineX device adapter

Component adapter 54 mm. Snap-on mounting of components.



Features

| | |
|------------------------------------|--|
| Model No. | RX 9360.760 |
| Version | With connection cable |
| Benefits | For mounting equipment for top-hat rail mounting, e.g. motor starter Pre-assembled connection cable Simple connector lock for component support rails Optional component anti-slip guard Snap-on mounting and easy adjustment on busbar thickness 5/10 mm Easy mounting Reduction of article variety through coordinated accessories |
| Material | Polyamide (PA 6) Fire behavior corresponding to UL 94 |
| Color | RAL 9005 RAL 35745 |
| Connection cables (AWG) | AWG 6 |
| Rated current (max.) | 65 A |
| Rated current of round conductor | 65 A |
| Rated current round conductor (UL) | 65 A |

Features

| | |
|--|---|
| Electrical UL ratings (SCCR) | 100 kA - 600 V, fuse class RK5 max. 60 A, JDDZ/7 20 kA - 600 V, circuit breaker max. 60 A, DIVQ/7 65 kA - 480 V, Combination Motor Controller max. 52 A, NKJH/7 |
| Cable outlet | Bottom |
| For bar systems with center-to-center spacing | 60 mm |
| Length of connection cable | 130 mm 5.12 " |
| Number of poles | 3-pole |
| Suitable for busbar system | RiLineX RiLine60 |
| Dimensions | Width: 54 mm Height: 239.4 mm Depth: 36.2 mm Width: 2.13 " Height: 9.43 " Depth: 1.43 " |
| Support rails Qty/height | 1 / 10 mm 0.39 " |
| Suitable for busbars | 15 x 5/10 20 x 5/10 30 x 5/10 |
| Rated voltage | 690 V AC 600 V AC (UL) 600 V DC (UL) |
| Contamination level | 3 |
| Standards | IEC 61 439-1/-2 UL 508 |
| Rated impulse withstand voltage U _{Imp} | 8 kV |
| Rated insulation voltage U _i | 1,000 V |
| Protection category IP to IEC 60529 | IP 2XB |

Features

| | |
|-----------------------------------|--|
| Maximum operating air humidity | 90 % |
| Operating temperature range | -5 °C...55 °C 23 °F...131 °F |
| Storage temperature range | -25 °C...75 °C -13 °F...167 °F |
| Ambient humidity (non-condensing) | 10...90 % |
| Packaging unit | 4 pc(s). |
| Net weight | 1.84 kg |
| Gross weight | 1.883 kg |
| Copper weight (kg per piece) | 0.145 |
| PCF/VE (cradle-to-gate) | 13.53 |
| Customs tariff number | 85369095 |
| ETIM 9 | EC001531 |
| Product description | RX component adapter 65 A, AWG 6, 3-pole, W: 54 mm |

Approvals

| | |
|--------------|--|
| Approvals | UL + C-UL (listed) |
| Explanations | Declaration of conformity PCF-declaration |