

# Rittal – The System.

Faster – better – everywhere.



## RX 9360.802

### RiLineX bus-mounting fuse element

State: 2/13/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL


IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# RX 9360.802 - RiLineX bus-mounting fuse element

RiLineX bus-mounting fuse element for 60 mm busbar systems. For fuse D 01 (with fitting ring) and D 02 (E18). With optical LED fuse monitoring. For safe contacting of the fuse, the device does not have screw caps, but fuse holders that can be locked when open and sealed when closed. A tension clamp terminal up to 16 mm<sup>2</sup> at an angle of 45° facilitates conductor connection. The device is suitable for tool-free snap-on installation and has a semi-automatic rail adjustment for 5 and 10 mm.



## Features

Model No.	RX 9360.802
Benefits	<p>Safe contacting of the fuse links (without screw caps)</p> <p>Snap-on mounting and easy adjustment on busbar thickness 5/10 mm</p> <p>Optical LED fuse monitoring</p> <p>Voltage test through separate opening</p> <p>Maintenance-free tension spring connection up to 16 mm<sup>2</sup></p> <p>Complete contact protection without additional accessories such as screw caps</p>
Product changes	(secondary)
Material	<p>Polyamide (PA 6)</p> <p>Fire protection corresponding to UL 94-V0</p>
Color	<p>RAL 35745</p> <p>RAL 9005</p>
Supply includes	<p>4 bus-mounting fuse elements</p> <p>12 reducers for D 01 fuses</p>

# Features

Rated current max.	63 A
Cable outlet	Bottom
Number of poles	3-pole
Suitable for busbar system	RiLineX RiLine60
Dimensions	Width: 26.8 mm Height: 253.8 mm Depth: 89.8 mm Width: 1.06 " Height: 9.99 " Depth: 3.54 "
Connection of round conductors, fine wire with wire end ferrule	1.5 - 16 mm <sup>2</sup>
Connection of round conductors, fine wire with wire end ferrule AWG	AWG 16 - AWG 6
Connection of round conductors, multi-wire	1.5 - 16 mm <sup>2</sup>
Connection of round conductors, multi-wire AWG	AWG 16 - AWG 6
Suitable for busbars	Height: 5, 10 mm Height: 0.2, 0.39 "
Suitable for busbars	15 x 5/10 20 x 5/10 30 x 5/10
Rated voltage	400 V AC
Overvoltage category	4
Contamination level	3
Standards	IEC 60 947-3
Rated insulation voltage Ui	1,000 V
Power dissipation (max.)	5.5 W 19 BTU/h

## Features

Protection category IP to IEC 60529	IP 2XB
Operation humidity max.	90 %
Operating temperature range	-5 °C...55 °C 23 °F...131 °F
Storage temperature range	-25 °C...75 °C -13 °F...167 °F
Ambient humidity (non-condensing)	10...90 %
Utilization category	AC-21B (400 V/100 A)
Fuse inserts	D 02-E 18
Packaging unit	4 pc(s).
Net weight	1.432
Gross weight	1.437
Copper weight (kg per piece)	0.07
Customs tariff number	85369095
ETIM 9	EC001644

## Approvals

## Explanations Declaration of conformity