Rittal – The System.

Faster – better – everywhere.



SV 9665.750

Cable entry flange

State: 11/13/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SV 9665.750 - Cable entry flange for roof plate

Cable entry gland for roof plates, with metric knockouts, seal membranes, cable entry glands, or solid.



Features

Model No.	SV 9665.750
Version	14 x M25/32
Product description	For simple, secure cable entry in the roof zone.
Material	Insulating material
Color	RAL 7035
Supply includes	Seal
No. of metric knockouts	14 x M25/M32
Dimensions	Width: 250 mm Depth: 160 mm Width: 9.84 ″ Depth: 6.3 ″
Protection category IP to IEC 60 529	IP 55
Packaging unit	1 pc(s).
Net weight	0.25 kg
Gross weight	0.279 kg
Customs tariff number	39269097
ETIM 9	EC000211

© Rittal 2026

Features

ECLASS 8.0	27142421
Product description	SV Cable entry gland, 14xM25/32, insulating material