

Rittal – The System.

Faster – better – everywhere.



SV 9665.750

Cable entry flange

State: 5/23/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9665.750 - Cable entry flange for roof plate

Cable entry gland for roof plates, with metric knockouts, seal membranes, cable entry glands, or solid.



Features

Model No.	SV 9665.750
Version	14 x M25/32
Product description	For simple, secure cable entry in the roof zone.
Material	Insulating material
Color	RAL 7035
Supply includes	Seal
No. of metric knockouts	14 x M25/M32
Dimensions	Width: 250 mm Depth: 160 mm Width: 9.84 " Depth: 6.3 "
Protection category IP to IEC 60529	IP 55
Packaging unit	1 pc(s).
Net weight	0.25 kg
Gross weight	0.279 kg
Customs tariff number	39269097
ETIM 9	EC000211

Features

ECLASS 8.0

27142421

Product description

SV Cable entry gland, 14xM25/32, insulating material