

Rittal – The System.

Faster – better – everywhere.



SV 9665.760 Cable entry flange

State: 7/10/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9665.760 - Cable entry flange for roof plate

Cable entry gland for roof plates, with metric knockouts, seal membranes, cable entry glands, or solid.



Features

| | |
|-------------------------------------|---|
| Model No. | SV 9665.760 |
| Version | 2 x M25/32/40, 1 x M32/40/50, 2 x M40/50/63 |
| Product description | For simple, secure cable entry in the roof zone. |
| Material | Insulating material |
| Color | RAL 7035 |
| Supply includes | Seal |
| No. of metric knockouts | 2 x M25/M32/M40 1 x M32/M40/M50 2 x M40/M50/M63 |
| Dimensions | Width: 250 mm Depth: 160 mm Width: 9.84 " Depth: 6.3 " |
| Protection category IP to IEC 60529 | IP 55 |
| Packaging unit | 1 pc(s). |
| Net weight | 0.25 kg |
| Gross weight | 0.281 kg |
| Customs tariff number | 39269097 |

Features

| | |
|---------------------|--|
| ETIM 9 | EC000211 |
| ECLASS 8.0 | 27142421 |
| Product description | SV Cable entry gland, 2xM25/32/40, 1xM32/40/50, 2xM40/50/63, insulating material |
