


Rittal – The System.

Faster – better – everywhere.



SV 9666.340

Connection terminal block

State: 6/18/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9666.340 - Connection terminal block

To connect copper and aluminum conductors and laminated copper bars.

Features

| | |
|---|---|
| Model No. | SV 9666.340 |
| Product description | For connecting copper and aluminum conductors. For laminated copper bars or solid and stranded conductors with crimped ferrules. |
| Material | Duroplastic |
| Color | RAL 7035 |
| Supply includes | Assembly components |
| Mounting tip | Contact hazard protection module 9666.020 is required to cover the connection terminal block |
| Rated current max. | 250 A |
| Number of poles | 5-pole |
| Connection of round conductors | 16 - 150 2 x 16 - 70 |
| Clamping area for laminated copper bars (W x H) | 17 x 21 mm 0.67 x 0.83 " |
| Packaging unit | 1 pc(s). |
| Net weight | 3.013 kg |
| Gross weight | 3.213 kg |
| Customs tariff number | 39211900 |
| ETIM 9 | EC001894 |
| ECLASS 8.0 | 27400613 |
| Product description | SV Connection terminal block (ISV), 250 A, 690 V, 5-pole, round conductor connection, 1x16-150/2x16-70 mm ² , clamping area BH: 17x21 mm |

Approvals

Explanations

Declaration of conformity

Declaration of conformity UK