

# Rittal – The System.

Faster – better – everywhere.



## RX 9362.000

# RiLineX NH fuse switch disconnecter

State: 7/10/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# RX 9362.000 - RiLineX NH fuse switch disconnecter

RiLineX NH fuse-switch-disconnector in size 00 for 60 mm busbar systems. The cover is lockable, sealable and features visual fuse monitoring. The safe voltage test takes place via the integrated measurement points on the cover. The NH fuse-switch-disconnecters have a park position to simplify maintenance work. Connection version with size M8 screw connection. Cable outlet can be individually converted at the top or bottom.



## Features

Model No.	RX 9362.000
Version	For 60 mm busbar systems
Benefits	Cover, lockable and sealable Voltage test through separate opening Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm Tool-free conversion of the cable outlet Park position for simplified maintenance work All variants also with electronic fuse monitoring
Material	Polyamide (PA 6) Fire behavior corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated
Color	RAL 9005 RAL 35745
For bar systems with center-to-center spacing	60 mm
Cable outlet	Top/bottom

# Features

Type of connection (electrical)	Screw M8
Fuse inserts	NH 00 NH 000
Rated operating voltage	690 V AC
For NH size	00
Test specification	IEC 60 947-3 IEC 60 269-2 (fuse inserts)
Dimensions	Width: 106 mm Height: 194.2 mm Depth: 104.5 mm Width: 4.17 " Height: 7.65 " Depth: 4.11 "
Operating temperature range	-5 °C...35 °C 23 °F...95 °F
Storage temperature range	-25 °C...70 °C -13 °F...158 °F
Suitable for busbars	15 x 5/10 20 x 5/10 30 x 5/10
Suitable for busbar system	RiLine60 RiLineX
Number of poles	3-pole
Utilization category	AC-23B (400 V/100 A) AC-22B (500 V/100 A) AC-21B (690 V/100 A) DC-22B (250 V/100 A)
Contamination level	3
Protection category IP to IEC 60529	IP 2XB
Fire load	14.2 MJ/m <sup>2</sup>
Power loss max.	19 W 65 BTU/h

## Features

---

Heat loss per fuse insert (max.)	12 W
Packaging unit	1 pc(s).
Net weight	1.015 kg
Gross weight	1.023 kg
Copper weight (kg per piece)	0.363
PCF/VE (cradle-to-gate)	6.85
Customs tariff number	85369095
ETIM 9	EC001040
Product description	RX NH fuse-switch-disconnector size 00, 160 A, 3-pole, M8 screw

## Approvals

---

Approvals	CQC-CCC
Explanations	Declaration of conformity PCF-declaration