Rittal – The System.

Faster – better – everywhere.





VX 9666.916 Baying-enclosure system VX25

State: 11/4/2025 (Source: rittal.com/us-en)



VX 9666.916 - Baying-enclosure system VX25 Distribution enclosures

VX baying system used as a distribution enclosure and prepared for ISV expansion module.







Features

Model No.	VX 9666.916
Material	Carbon steel
Surface finish	Enclosure frame: Dipcoat-primed
	Door(s), roof, rear panel: Dipcoat-primed, powder-coated on the
	outside, textured paint
	Base plates: Zinc-plated
Color	RAL 7035
Supply includes	Enclosure frame
	Door(s)
	Door hinged on the right, may be swapped to the left
	Base Plates
	Rear panel
	Roof plate
	Lock: 3 mm double-bit
Number of doors	1
Note	Use VX basic enclosures for 600 mm wide installation divider
	For a base/plinth height of 200 mm, 2 packs each of plinth corne
	pieces, 100 mm and base/plinth trim panels, 100 mm are require

© Rittal 2025

Features

Protection category IP to IEC 60 529	IP 55
Protection category NEMA	NEMA 12
Test specification	IEC 61 439-1/-2
Dimensions	Width: 850 mm
	Height: 2,000 mm
	Depth: 600 mm
	Width: 33.5 "
	Height: 78.7 "
	Depth: 23.6 "
Packaging unit	1 pc(s).
Net weight	89.2
Gross weight	91.6
PCF/VE (cradle-to-gate)	288.3 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	94032080
EAN	4028177929722
ETIM 9	EC000214
ECLASS 8.0	27142409

Approvals

Approvals	Bureau Veritas DNV-GL
Certificates	Surface finish
Explanations	Declaration of conformity UK

© Rittal 2025 3