Rittal – The System.

Faster – better – everywhere.



RX 9362.005

RiLineX NH fuse switch disconnector

State: 11/5/2026 (Source: www.rittal.com/us-en)

RX 9362.005 - RiLineX NH fuse switch disconnector

RiLineX NH fuse-switch-disconnector in size 00 for 60 mm busbar systems. The cover is lockable, sealable and features visual fuse monitoring. The safe voltage test takes place via the integrated measurement points on the cover. The NH fuse-switch-disconnectors have a park position to simplify maintenance work. Connection version with M8 screw connection. Cable outlet can be individually converted at the top or bottom. Including electronic fuse monitoring.







Features

Model No.	RX 9362.005
Version	With electronic fuse monitoring For 60 mm busbar systems
Benefits	Cover, lockable and sealable Voltage test through separate opening Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm Tool-free conversion of the cable outlet Park position for simplified maintenance work All variants also with electronic fuse monitoring
Material	Polyamide (PA 6) Fire behavior corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated
Color	RAL 9005 RAL 35745
Supply includes	Incl. connection plug for electrical fuse monitoring

© Rittal 2026

Features

For bar systems with center-to-center spacing	60 mm
Cable outlet	Top/bottom
Type of connection (electrical)	Screw M8
Fuse inserts	NH 00
Rated operating voltage	1000 V AC
For NH size	00
Test specification	IEC 60 947-3 IEC 60 269-2 (fuse inserts)
Dimensions	Width: 106 mm Height: 229.5 mm Depth: 104.5 mm Width: 4.17 ″ Height: 9.04 ″ Depth: 4.11 ″
Operating temperature range	-5 °C...35 °C 23 °F...95 °F
Storage temperature range	-25 °C...70 °C -13 °F...158 °F
Suitable for busbars	15 x 5/10 20 x 5/10 30 x 5/10
Suitable for busbar system	RiLineX RiLine60
Number of poles	3-pole
Utilization category	AC-23B (400 V/160 A) AC-22B (500 V/160 A) AC-21B (690 V/160 A) AC-21B (800 V/63 A) AC-20B (1000 V/160 A) DC-22B (250 V/160 A) DC-21B (440 V/63 A) DC-20B (800 V/160 A) DC-20B (1000 V/160 A)

© Rittal 2026

Features

Contamination level	3
With electronic fuse monitoring	Yes
Protection category IP to IEC 60 529	IP 20
Fire load	16.6 MJ/m²
Power loss max.	19 W 65 BTU/h
Heat loss per fuse insert (max.)	12 W
Packaging unit	1 pc(s).
Net weight	1.135 kg
Gross weight	1.155 kg
Copper weight (kg per piece)	0.363
PCF/VE (cradle-to-gate)	7.71
Customs tariff number	85369095
ETIM 9	EC001040
Product description	RX NH fuse-switch-connector size 00, 160 A, 3-pole, M8 screw, with fuse monitoring 800 V

Approvals

Approvals	CQC-CCC
Explanations	Declaration of conformity PCF-declaration