## Rittal - The System.

Faster - better - everywhere.





# SV 9676.749 Connection Plate

State: 11/4/2025 (Source: rittal.com/us-en)



## SV 9676.749 - Connection Plate for laminated copper bars

For connection of laminated copper bars.

#### **Features**

Model No.	SV 9676.749
Product description	For connecting laminated copper bars to a distribution busbar system made of flat copper. Suitable for 10 mm rail thickness.
Material	Connection plate: E-Cu Pressure piece: Stainless steel Busbar claw: Stainless steel
Supply includes	Assembly parts (excluding screws)
Mounting tip	The required screw length must be selected according to the busbar width W, i.e., Length = W + fastening measurement. Screws are not included with the supply  Busbar claw with threaded insert M10
Number of bars per conductor	2
Mounting dimensions	50 mm 1.97 ″
Clamping area for laminated copper bars (W x H)	100 x 20 mm 3.94 x 0.79 ″
Suitable for laminated copper bars	Qty.: 2 Number of lamina: 10 Lamina width: 100 mm Lamina thickness: 1 mm Lamina width: 3.94 " Lamina thickness: 0.04 "
Packaging unit	1 pc(s).
Net weight	0.62
Gross weight	0.639
Copper weight (kg per piece)	0.62

© Rittal 2025

### Features

EAN	4028177625570
ETIM 9	EC002270
ECLASS 8.0	27400613

## **Approvals**

Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3