

Rittal – The System.

Faster – better – everywhere.



RX 9362.110 RiLineX NH fuse switch disconnecter

State: 4/25/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9362.110 - RiLineX NH fuse switch disconnecter

RiLineX NH fuse-switch-disconnector in size 1 for 60 mm busbar systems. The cover is lockable, sealable and features visual fuse monitoring. The safe voltage test takes place via the integrated measurement points on the cover. The NH fuse-switch-disconnecters have a park position to simplify maintenance work. Connection version with M10 screw connection. Cable outlet can be individually converted at the top or bottom.



Features

| | |
|---|---|
| Model No. | RX 9362.110 |
| Version | For 60 mm busbar systems |
| Benefits | Cover, lockable and sealable Voltage test through separate opening Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm Tool-free conversion of the cable outlet Park position for simplified maintenance work All variants also with electronic fuse monitoring |
| Material | Polyamide (PA 6) Fire behavior corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated |
| Color | RAL 9005 RAL 35745 |
| For bar systems with center-to-center spacing | 60 mm |
| Cable outlet | Top/bottom |
| Type of connection (electrical) | Screw M10 |
| Fuse inserts | NH 1 |

Features

| | |
|-------------------------------------|--|
| Rated operating voltage | 690 V AC |
| For NH size | 1 |
| Test specification | IEC 60 947-3 IEC 60 269-2 (fuse inserts) |
| Dimensions | Width: 181.5 mm Height: 298 mm Depth: 116.7 mm Width: 7.15 " Height: 11.7 " Depth: 4.59 " |
| Operating temperature range | -5 °C...35 °C 23 °F...95 °F |
| Storage temperature range | -25 °C...70 °C -13 °F...158 °F |
| Suitable for busbars | 15 x 5/10 20 x 5/10 30 x 5/10 |
| Suitable for busbar system | RiLineX RiLine60 |
| Number of poles | 3-pole |
| Utilization category | AC-23B (400 V/100 A) AC-22B (500 V/100 A) AC-21B (690 V/100 A) DC-22B (250 V/100 A) DC-21B (440 V/100 A) |
| Contamination level | 3 |
| Protection category IP to IEC 60529 | IP 2XB |
| Fire load | 36.19 MJ/m ² |
| Power loss max. | 51 W 174 BTU/h |
| Heat loss per fuse insert (max.) | 23 W |
| Packaging unit | 1 pc(s). |

Features

| | |
|------------------------------|---|
| Net weight | 2.273 kg |
| Gross weight | 2.448 kg |
| Copper weight (kg per piece) | 0.8 |
| Customs tariff number | 85369095 |
| ETIM 9 | EC001040 |
| Product description | RX NH fuse-switch-disconnector size 1, 250 A, 3-pole, M10 screw |

Approvals

| | |
|--------------|--|
| Explanations | Declaration of conformity PCF-declaration |
|--------------|--|