
Rittal – The System.

Faster – better – everywhere.



RX 9362.215

RiLineX NH fuse switch disconnector

State: 11/1/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

RX 9362.215 - RiLineX NH fuse switch disconnector

RiLineX NH fuse-switch-disconnector in size 2 for 60 mm busbar systems. The cover is lockable, sealable and features visual fuse monitoring. The safe voltage test takes place via the integrated measurement points on the cover. The NH fuse-switch-disconnectors have a park position to simplify maintenance work. Connection version with M10 screw connection. Cable outlet can be individually converted at the top or bottom. Including electronic fuse monitoring.







Features

Model No.	RX 9362.215
Version	For 60 mm busbar systems With electronic fuse monitoring
Benefits	Cover, lockable and sealable Voltage test through separate opening Tool-free conversion of the cable outlet Park position for simplified maintenance work All variants also with electronic fuse monitoring
Material	Polyamide (PA 6) Fire behavior corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated
Color	RAL 9005 RAL 35745
Supply includes	Incl. connection plug for electrical fuse monitoring
For bar systems with center-to-center spacing	60 mm

© Rittal 2026

Features

Cable outlet	Top/bottom
Type of connection (electrical)	Screw M10
Fuse inserts	NH 2
Rated operating voltage	690 V AC
For NH size	2
Test specification	IEC 60 947-3 IEC 60 269-2 (fuse inserts)
Dimensions	Width: 208.5 mm Height: 348.7 mm Depth: 134.6 mm Width: 8.21 ″ Height: 13.7 ″ Depth: 5.3 ″
Operating temperature range	-5 °C...35 °C 23 °F...95 °F
Storage temperature range	-25 °C...70 °C -13 °F...158 °F
Suitable for busbars	15 x 5/10 20 x 5/10 30 x 5/10
Suitable for busbar system	RiLineX RiLine60
Number of poles	3-pole
Utilization category	AC-23B (400 V/400 A) AC-22B (500 V/400 A) AC-22B (690 V/400 A) AC-23B (690 V/315 A) AC-21B (800 V/200 A) AC-20B (1000 V/400 A) DC-22B (250 V/400 A) DC-22B (440 V/400 A) DC-20B (800 V/400 A) DC-20B (1000 V/400 A)
Contamination level	3

© Rittal 2026

Features

With electronic fuse monitoring	Yes
Protection category IP to IEC 60 529	IP 20
Fire load	46.16 MJ/m²
Power loss max.	98 W 334 BTU/h
Packaging unit	1 pc(s).
Net weight	4.2 kg
Gross weight	4.268 kg
Copper weight (kg per piece)	1.75
PCF/VE (cradle-to-gate)	28.53
Customs tariff number	85369095
ETIM 9	EC001040
Product description	RX NH fuse-switch-connector size 2, 400 A, 3-pole, M10 screw, with fuse monitoring 800 V

Approvals

Approvals	CQC-CCC
Explanations	Declaration of conformity PCF-declaration