

Rittal – The System.

Faster – better – everywhere.



RX 9362.216

**RiLineX NH fuse switch
disconnecter**

State: 4/26/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9362.216 - RiLineX NH fuse switch disconnecter

RiLineX NH fuse switch disconnectors, size 2, for 60 mm busbar systems. The cover can be locked, sealed and has visual fuse monitoring. Safe voltage testing is carried out via integrated measuring points on the cover. The NH fuse switch disconnectors have a park position to make the maintenance work easier. Connection design with screwed connection, size M10. Cable outlet can be individually configured to be at the top or bottom. Includes electronic fuse monitoring. Suitable for voltage range between 180 and 400 V.



Features

Model No.	RX 9362.216
Version	For 60 mm busbar systems
Benefits	Cover, lockable and sealable Voltage test through separate opening Tool-free conversion of the cable outlet Park position for simplified maintenance work
Material	Polyamide (PA 6) Fire behavior corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated
Color	RAL 9005 RAL 35745
For bar systems with center-to-center spacing	60 mm
Cable outlet	Top/bottom
Type of connection (electrical)	Screw M10
For NH size	2
Test specification	IEC 60 947-3 IEC 60 269-2 (fuse inserts)

Features

Dimensions	Width: 209 mm Height: 349 mm Depth: 135 mm Width: 8.23 " Height: 13.7 " Depth: 5.31 "
------------	--

Operating temperature range	-5 °C...35 °C 23 °F...95 °F
-----------------------------	--------------------------------

Storage temperature range	-25 °C...70 °C -13 °F...158 °F
---------------------------	-----------------------------------

Suitable for busbars	15 x 5/10 20 x 5/10 30 x 5/10
----------------------	-------------------------------------

Number of poles	3-pole
-----------------	--------

Utilization category	AC-23B (400 V/100 A) AC-22B (500 V/100 A) AC-21B (690 V/100 A) DC-22B (250 V/100 A)
----------------------	--

Contamination level	3
---------------------	---

Protection category IP to IEC 60529	IP 2XB
-------------------------------------	--------

Fire load	46.16 MJ/m ²
-----------	-------------------------

Power loss max.	98 kW 334,390 BTU/h
-----------------	------------------------

Packaging unit	1 pc(s).
----------------	----------

Net weight	3.8 kg
------------	--------

Gross weight	4.251 kg
--------------	----------

Customs tariff number	85369095
-----------------------	----------

Features

Product description

RiLineX NH fuse switch disconnectors, size 2, for 60 mm busbar systems. The cover can be locked, sealed and has visual fuse monitoring. Safe voltage testing is carried out via integrated measuring points on the cover. The NH fuse switch disconnectors have a park position to make the maintenance work easier. Connection design with screwed connection, size M10. Cable outlet can be individually configured to be at the top or bottom. Includes electronic fuse monitoring. Suitable for voltage range between 180 and 400 V.

Approvals

Explanations

Declaration of conformity