

# Rittal – The System.

Faster – better – everywhere.



## RX 9362.250

### RiLineX NH fuse switch disconnector

State: 2/12/2026 (Source: [ittal.com/us-en](http://ittal.com/us-en))



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# RX 9362.250 - RiLineX NH fuse switch disconnector

RiLineX NH fuse-switch-disconnector in size 2 for 60 mm busbar systems. The cover is lockable, sealable and features visual fuse monitoring. The safe voltage test takes place via the integrated measurement points on the cover. The NH fuse-switch-disconnectors have a park position to simplify maintenance work. Connection design with box terminal for connecting round conductors min. 120 bis max. 300 mm<sup>2</sup>. Cable outlet can be individually converted at the top or bottom.



## Features

Model No.	RX 9362.250
Version	For 60 mm busbar systems
Benefits	Cover, lockable and sealable Voltage test through separate opening Tool-free conversion of the cable outlet Park position for simplified maintenance work All variants also with electronic fuse monitoring
Material	Polyamide (PA 6) Fire behavior corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated
Color	RAL 9005 RAL 35745
For bar systems with center-to-center spacing	60 mm
Cable outlet	Top/bottom
Type of connection (electrical)	Box terminal
Rated current max.	400 A
Rated operating current max.	400 A

# Features

Rated operating voltage	690 V AC
For NH size	2
Test specification	IEC 60 947-3 IEC 60 269-2 (fuse inserts)
Dimensions	Width: 208.5 mm Height: 298.6 mm Depth: 134.6 mm Width: 8.21 " Height: 11.8 " Depth: 5.3 "
Operating temperature range	-5 °C...35 °C 23 °F...95 °F
Storage temperature range	-25 °C...70 °C -13 °F...158 °F
Suitable for busbars	15 x 5/10 20 x 5/10 30 x 5/10
Suitable for busbar system	RiLineX RiLine60
Number of poles	3-pole
Contamination level	3
Protection category IP to IEC 60 529	IP 2XB
Fire load	50.96 MJ/m <sup>2</sup>
Connection of round conductors, fine wire without wire end ferrule	35 - 240 mm <sup>2</sup>
Connection of round conductors, fine wire with wire end ferrule	35 - 240 mm <sup>2</sup>
Power dissipation (max.)	98 W 334 BTU/h
Packaging unit	1 pc(s).
Net weight	4.25

# Features

Gross weight	4.37
Copper weight (kg per piece)	1.75
Customs tariff number	85369095
ETIM 9	EC001040

## Approvals

## Explanations Declaration of conformity