

Rittal – The System.

Faster – better – everywhere.



SV 9677.710 Component Adapters

State: 6/3/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9677.710 - Component Adapters Terminal fastening

For circuit breakers from ABB, Eaton, Schneider Electric and Siemens. For rail systems with 185 mm center-to-center distance.

Features

Model No.	SV 9677.710
Material	Polyamide Fire protection corresponding to UL 94-V0
Color	RAL 7035
For bar systems with center-to-center spacing	185 mm
Cable outlet	Bottom
Installation type	Clamping attachment
Number of poles	3-pole
Rated current max.	1,600 A
Rated operating voltage	690 V, 3~
Note	Cable outlet: Switch outlet or as outgoing cable from the switchgear Suitable for the use of switchgear with front screw terminal For mounting on busbar systems with or without cover section
Dimensions	Width: 300 mm Height: 652 mm Width: 11.8 " Height: 25.7 "
Suitable for busbars	Height: 10 mm Height: 0.39 "
To fit manufacturer (model)	ABB (XT7 – 1250 A/1600 A) Eaton (NZM4 - 1250 A/1600 A) Schneider Electric (NS - 1250 A/1600 A) Siemens (3VA27 - 1250 A/1600 A)
Packaging unit	1 pc(s).
Net weight	21.12 kg

Features

Gross weight	22.2 kg
Copper weight (kg per piece)	14.68
Customs tariff number	85369095
ETIM 9	EC001531
ECLASS 8.0	27370304
Product description	SV Component adaptor, 1600 A, 690 V, 3-pole, 185 mm, clamping attachment

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK