

Rittal – The System.

Faster – better – everywhere.



SV 9677.715 Component Adapters

State: 4/21/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9677.715 - Component Adapters Screw fastening

For circuit breakers from ABB, Eaton, Schneider Electric and Siemens. For rail systems with 185 mm center-to-center distance.

Features

| | |
|---|---|
| Model No. | SV 9677.715 |
| Material | Polyamide Fire protection corresponding to UL 94-V0 |
| Color | RAL 7035 |
| For bar systems with center-to-center spacing | 185 mm |
| Cable outlet | Bottom |
| Installation type | Screw attachment |
| Number of poles | 3-pole |
| Rated current max. | 1,600 A |
| Rated operating voltage | 690 V, 3~ |
| Note | Cable outlet: Switch outlet or as outgoing cable from the switchgear Suitable for the use of switchgear with front screw terminal for fastening to perforated busbars. Note that no cover sections are fitted in the vicinity of the device. |
| Dimensions | Width: 300 mm Height: 652 mm Width: 11.8 " Height: 25.7 " |
| Suitable for busbars | Height: 10 mm Height: 0.39 " |
| To fit manufacturer (model) | ABB (Tmax T7 - 1250 A/1600 A) Eaton (NZM4 - 1250 A/1600 A) Schneider Electric (NS - 1250 A/1600 A) Siemens (3VA27 - 1250 A/1600 A) |
| Packaging unit | 1 pc(s). |

Features

| | |
|------------------------------|---|
| Net weight | 19.34 kg |
| Gross weight | 21.4 kg |
| Copper weight (kg per piece) | 14.749 |
| Customs tariff number | 85369095 |
| ETIM 9 | EC001531 |
| ECLASS 8.0 | 27370304 |
| Product description | SV Component adaptor, 1600 A, 690 V, 3-pole, 185 mm, screw attachment |

Approvals

| | |
|--------------|---|
| Approvals | UL + C-UL (listed) |
| Explanations | Declaration of conformity Declaration of conformity UK |