

# Rittal – The System.

Faster – better – everywhere.



## RX 9363.030

# RiLineX NH fuse switch disconnecter

State: 6/10/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# RX 9363.030 - RiLineX NH fuse switch disconnecter

RiLineX NH fuse-switch-disconnector in sizes 00 for mounting plates. The cover is lockable, sealable and features visual fuse monitoring. The safe voltage test takes place via the integrated measurement points on the cover. The NH fuse-switch-disconnecters have a park position to simplify maintenance work. Connection design with box terminal for connecting round conductors min. 1.5 bis max. 95 mm<sup>2</sup>.



## Features

---

Model No.	RX 9363.030
-----------	-------------

---

Version	For mounting panel assembly.
---------	------------------------------

---

Benefits	Cover, lockable and sealable Voltage test through separate opening Tool-free conversion of the cable outlet Park position for simplified maintenance work All variants also with electronic fuse monitoring
----------	-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

---

Material	Polyamide (PA 6) Fire behavior corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated
----------	----------------------------------------------------------------------------------------------------------------

---

Color	RAL 9005 RAL 35745
-------	-----------------------

---

for mounting plate assembly	Yes
-----------------------------	-----

---

Cable outlet	Top/bottom
--------------	------------

---

Type of connection (electrical)	Box terminal
---------------------------------	--------------

---

# Features

Fuse inserts	NH 00 NH 000
Rated insulation voltage $U_i$	1,000 kV
Rated operating voltage	690 V AC
For NH size	00
Test specification	IEC 60 947-3 IEC 60 269-2 (fuse inserts)
Dimensions	Width: 106 mm Height: 194 mm Depth: 86.1 mm Width: 4.17 " Height: 7.64 " Depth: 3.39 "
Connection of round conductors	1.5 - 16 mm <sup>2</sup>
Operating temperature range	-5 °C...35 °C 23 °F...95 °F
Storage temperature range	-25 °C...70 °C -13 °F...158 °F
Number of poles	3-pole
Utilization category	AC-23B (400 V/100 A) AC-22B (500 V/100 A) AC-21B (690 V/100 A) DC-22B (250 V/100 A)
Contamination level	3
Protection category IP to IEC 60 529	IP 2XB
Fire load	11.56 MJ/m <sup>2</sup>
Connection of round conductors, fine wire without wire end ferrule	1.5 - 95 mm <sup>2</sup>
Connection of round conductors, fine wire with wire end ferrule	1.5 - 95 mm <sup>2</sup>
Round conductor cross-section	1.5 - 16 mm <sup>2</sup>

# Features

---

Power loss max.	16 W 55 BTU/h
Heat loss per fuse insert (max.)	12 W
Packaging unit	1 pc(s).
Net weight	0.809 kg
Gross weight	0.829 kg
Copper weight (kg per piece)	0.268
PCF/VE (cradle-to-gate)	5.47
Customs tariff number	85369095
ETIM 9	EC001040
Product description	RX NH fuse-switch-disconnector size 00, 160 A, 3-pole, box terminal, mounting plate assembly

---

# Approvals

---

Approvals	CQC-CCC
Explanations	Declaration of conformity PCF-declaration

---