

# Rittal – The System.

Faster – better – everywhere.



## SV 9677.910 Connection block

State: 4/3/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9677.910 - Connection block

For connecting cables and laminated copper bars.

## Features

|                                     |  |
|-------------------------------------|--|
| Model No.                           | SV 9677.910  |
| Product description                 | For connecting conductors or laminated copper bars.  |
| Material                            | Carbon steel, zinc-plated<br>E-Cu, tin-plated  |
| Clamping area height                | 20 mm<br>0.79 "  |
| Clamping area width                 | 80 mm<br>3.15 "  |
| Cable outlet                        | Top/bottom   |
| Rated current max.                  | 1,600 A  |
| Dimensions                          | Width: 98 mm<br>Width: 3.86 "  |
| Suitable for busbars                | Height: 10 mm<br>Height: 0.39 "  |
| Packaging unit                      | 1 pc(s).   |
| Net weight                          | 0.9 kg   |
| Gross weight                        | 0.982 kg   |
| Copper weight (kg per piece)        | 0.689  |
| PCF/VE (cradle-to-gate)             | 3.7 kg CO2 eq (Cat B)  |
| Information regarding the PCF class | Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared |
| Customs tariff number               | 85369095   |
| ETIM 9                              | EC002270   |
| ECLASS 8.0                          | 27400613   |

# Features

---

|                     |   |
|---------------------|---|
| Product description | SV Connection block, 1600 A, 690 V, 1-pole, cable outlet top/bottom |
|---------------------|---|

# Approvals

---

|           |                    |
|-----------|--------------------|
| Approvals | UL + C-UL (listed) |
|-----------|--------------------|

---

|              |                              |
|--------------|------------------------------|
| Explanations | Declaration of conformity    |
|              | Declaration of conformity UK |