

Rittal – The System.

Faster – better – everywhere.



RX 9363.315

RiLineX NH fuse switch disconnecter

State: 4/25/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9363.315 - RiLineX NH fuse switch disconnecter

RiLineX NH fuse-switch-disconnector in sizes 3 for mounting plates. The cover is lockable, sealable and features visual fuse monitoring. The safe voltage test takes place via the integrated measurement points on the cover. The NH fuse-switch-disconnecters have a park position to simplify maintenance work. Connection version with M10 screw connection. Including electronic fuse monitoring.



Features

| | |
|-----------------------------|---|
| Model No. | RX 9363.315 |
| Version | For mounting panel assembly. |
| Benefits | Cover, lockable and sealable Voltage test through separate opening Tool-free conversion of the cable outlet Park position for simplified maintenance work All variants also with electronic fuse monitoring |
| Material | Polyamide (PA 6) Fire behavior corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated |
| Color | RAL 9005 RAL 35745 |
| Supply includes | Incl. connection plug for electrical fuse monitoring |
| for mounting plate assembly | Yes |
| Cable outlet | Top/bottom |

Features

| | |
|--------------------------------------|--|
| Type of connection (electrical) | Screw M10 |
| Fuse inserts | NH 3 |
| Rated insulation voltage U_i | 1,000 kV |
| Rated operating voltage | 690 V AC |
| For NH size | 3 |
| Test specification | IEC 60 947-3 IEC 60 269-2 (fuse inserts) |
| Dimensions | Width: 250 mm Height: 348.6 mm Depth: 128.7 mm Width: 9.84 " Height: 13.7 " Depth: 5.07 " |
| Operating temperature range | -5 °C...35 °C 23 °F...95 °F |
| Storage temperature range | -25 °C...70 °C -13 °F...158 °F |
| Number of poles | 3-pole |
| Contamination level | 3 |
| With electronic fuse monitoring | Yes |
| Protection category IP to IEC 60 529 | IP 2XB |
| Fire load | 50.46 MJ/m ² |
| Power loss max. | 84 W 287 BTU/h |
| Packaging unit | 1 pc(s). |
| Net weight | 4.21 kg |
| Gross weight | 4.216 kg |
| Copper weight (kg per piece) | 1.68 |
| Customs tariff number | 85369095 |

Features

ETIM 9

EC001040

Product description

RX NH fuse-switch-disconnector size 3, 630 A, 3-pole, M10 screw, with fuse monitoring 800 V, mounting plate assembly

Approvals

Explanations

Declaration of conformity
PCF-declaration