

Rittal – The System.

Faster – better – everywhere.



RX 9364.002 RiLineX fuse holder

State: 5/22/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9364.002 - RiLineX fuse holder

Compact RiLineX fuse holder class CC for 60 mm busbar systems. For cylinder fuse class CC (30 A) with optical LED fuse monitoring. For safe contacting of the cylinder fuses, the device has special fuse holders that can be locked when open and sealed when closed. Tension clamp terminals up to 6 mm² at an angle of 45° make it easier to connect conductors. The device is suitable for tool-free snap-on installation with semi-automatic rail adjustment for 5 and 10 mm.



Features

Model No.	RX 9364.002
Benefits	Compact width Snap-on mounting and easy adjustment on busbar thickness 5/10 mm For Class CC fuse to UL 248-4 UL-listed, approved to UL 4248 Innovative swivel mechanism, selective replacement of individual fuse inserts supported Readily accessible push-in connections in the lower section Fuse removal tools included with the supply Can be locked and prepared for a lead seal
Material	Polyamide (PA 6) Fire protection corresponding to UL 94-V0
General color	RAL 9005 RAL 35745
Rated current (max.)	30 A
Type of connection (electrical)	Spring terminal

Features

Rated operating voltage	600 V AC
Electrical UL ratings (SCCR)	200 kA - 600 V, fuse class CC max. 30 A, JDDZ/7
Number of poles	3-pole
Dimensions	Width: 18 mm Height: 263 mm Depth: 123.5 mm Width: 0.71 " Height: 10.4 " Depth: 4.86 "
Connection of round conductors, fine wire with wire end ferrule	1.5 - 6 mm ²
Suitable for busbars	15 x 5/10 20 x 5/10 30 x 5/10
Fuse inserts	Class CC
For fuse type (class)	Fuse class CC
Packaging unit	4 pc(s).
Net weight	1 kg
Gross weight	1.013 kg
Customs tariff number	85369095

Approvals

Approvals	UL + C-UL (listed)
-----------	--------------------